

RF skin tighten machine

Detailed Product Description

Skin & large pores tightening,

Wrinkles Removal,

Activate collagen tissue,

improve the skin flexibility,

Face&Body lifting

Electrical requirement	220VAC 50-60Hz 2A
Temperature of probes	0-5
Working mode of hand piece	Intermittent/continuous
Energy Density	0-100J/cm ²
Energy Delivery	By brass tips with golden plated
Working Frequency	11MHz
Delay time	50ms-1000ms
RF interval	0.25s-2.00s
Repetition Rate	1-5Hz
power	250W
Dimension	300mmX400mmX900mm
N.W.	45KGS